

## Compact Digital Multimeter



- 3½ digit LCD display
- Integrated test leads with neat stowaway design
- Diode test and audible continuity test
- Data hold
- Low battery indication and overload protection

Function	Max. Range	Basic Accuracy
DC Voltage	600V	±(0.5%+3d)
AC Voltage	600V	±(0.8%+4d)
DC Current	400mA	±(2.0%+3d)
AC Current	400mA	±(3.0%+4d)
Resistance	40MΩ	±(1.0%+3d)
Frequency	100kHz	±(0.5%+3d)
Capacitance	100μF	±(3.0%+3d)

### Physical Specifications

Power	2x SR44
Dimensions (WxHxD)	70 x 120 x 18mm
Weight	170g

**Includes:** carry pouch, batteries and user manual.

**Order Code**  
**133-9601**