

Mini Digital Clamp Meter



- Large 4000 count LCD display
- 1mA, high resolution
- Wide measuring range from small to large currents
- Diode check and Continuity buzzer
- 12.5mm jaw capacity
- Data Hold and Max hold functions
- Auto power off
- Safety Category: CATIII 600V

Includes: 9V battery, test leads and carry case

Function	Range	Basic Accuracy	Best Resolution
DC Current	4A, 80A	$\pm(2.5\%+4d)$	1mA
AC Current	4A, 80A	$\pm(2.5\%+5d)$	1mA
DC Voltage	400mV - 600V	$\pm(1.5\%+3d)$	0.1mV
AC Voltage	400mV - 600V	$\pm(2.0\%+4d)$	0.1mV
Resistance	400 Ω - 40M Ω	$\pm(1.5\%+2d)$	0.1 Ω
Frequency	5Hz - 10MHz	$\pm(1.2\%+3d)$	0.001Hz
Duty Cycle	5% - 99.9%	$\pm(1.2\%+3d)$	0.1%

Physical Specifications

Power	1x 9V PP3
Dimensions (WxHxD)	70 x 210 x 37mm
Weight	200g

Model	Order Code
3340	143-0687