
INDUSTRIAL pH INSTRUMENTATION & ELECTRODES

Retractable Flat Surface pH/ORP Electrodes for Insertion into Tanks and Main Lines



- Acrylamide Gel Standard
- Can Be Installed in Any Direction
- Retractable Design Allows Removal Without System Shutdown
- **Detachable Electrode for Easy** Maintenance and Removal

The PHE-6820B electrode and assembly features a retractable design for insertion into tanks and main lines. The assembly, when used with a 1" full port or larger ball valve (user supplied), allows the electrode to be removed without shutting the system down. This electrode can be mounted in any location, even up through the bottom of a tank with the electrode surface facing upward. Its unique design affords mounting in any direction and is suitable for most systems' inherent design.

The flat surface design minimizes fouling and coating and eliminates electrode breakage. Turbulent flow across the electrode surface results in a scrubbing action that keeps the electrode clean. The flat surface electrode is specifically designed for difficult applications such as oily waste water, emulsions, lime slurries, and flocculants.

SPECIFICATIONS

Maximum Temperature Standard Models: 87°C (190°F) CPVC body 100°C (212°F) PVDF body Mounting Assembly: CPVC or PVDF, FKM O-Rings; 1 MNPT Pipe thread Available Options:

"-HF" Fluoride resistant, for additional cost "-LC" Low conductivity, for additional cost

"-GL" Ground loop, for additional cost

Flectrodes

Electrodes		
To Order		
Model No.	Description	
PHE-6820B	pH electrode, CPVC	
PHE-6821	pH electrode, PVDF	
ORE-6820B	ORP electrode, CPVC	
ORE-6821	ORP electrode, PVDF	
Mounting Assemblies — Required for Installation		
PHEH-68-10	305 mm (12") CPVC without ATC	
PHEH-68K-10	305 mm (12") PVDF without ATC	
PHEH-68-10-(*)	305 mm (12") CPVC with ATC	
PHEH-68K-10-(*)	305 mm (12") PVDF with ATC	
PHEH-6820	457 mm (18") CPVC without ATC	
PHEH-6830	610 mm (24") CPVC without ATC	

Note: Temperature compensation is not required with ORP electrodes.

Order electrode and mounting assemblies separately. Materials of construction must be the same. Mounting assemblies come with 3 m (10') cable with BNC connector. Cable lengths available up to 15 m (50'), additional cost per extra foot. Consult Engineering for ordering information.

* Specify ATC Sensor

Order Code	Description
PT100	100 Ω Pt RTD
PT1K	1000 Ω Pt RTD
TH700	Series 700 thermistor
R3K	3000 Ω Balco

Note: At the time of initial purchase, please order both electrode and mounting assembly. Mounting assembly includes insertion assembly and cable. If ordered with automatic temperature compensation (ATC), the temperature compensator is built into the insertion assembly. When electrode has expired, simply re-order electrode.

Ordering Examples: PHE-6820B, CPVC pH electrode and PHEH-68-20, CPVC mounting assembly with 6 m (20') cable.

PHE-6821, PVDF pH electrode and **PHEH-68-10-PT100**, mounting assembly with 100 Ω Pt RTD ATC.