



Main

Range of product	8501X
Relay type	Utility
Product or component type	Relay
[In] rated current	10 A AC 5 A DC
Contacts type and composition	4 NO 4 standard contact cartridges
Poles description	4P
[Uc] control circuit voltage	125 V DC
Maximum switching voltage	250 V DC
Mounting support	Panel
Ambient air temperature for operation	-40...160 °F (-40...71 °C)
Electrical connection	Ring tongue
Product certifications	UL listed CE CSA
Operating time	37 ms - pick-up 21 ms - drop-out
Height	3.56 In (90.42 mm)
Width	2.23 In (56.64 mm)
Depth	5.17 In (131.32 mm)

Packing Units

Package 1 Weight	3.36 Lb(US) (1.524 kg)
------------------	------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------