

Product data sheet

Specifications



SELECTOR SWITCH OPERATOR 30MM SK

9001SKS401B

Main

Bezel material	Black plastic
Enclosure type	Dust and oil resistant weatherproof enclosure for indoor/outdoor
Range of product	K

Complementary

Accessory / separate part destination	Non illuminated push-button
Cap/Operator or lens colour	black
Contacts type and composition	Without contact block
Operator position information	3 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Size	30 mm
Type of operator	Maintained

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	58.967 g
Package 1 Height	19.355 cm
Package 1 width	7.62 cm
Package 1 Length	49.161 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov