

Product data sheet

Specifications



PUSH BUTTON 600VAC 10A 30MM T-K



9001KR1UH2

Main

Range of product	Harmony 9001K
Product or component type	Push-button
Device short name	K
Operator profile	White projecting Orange projecting Black projecting Red projecting Green projecting Yellow projecting Blue projecting
Operator additional information	Full guard in plastic

Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Light source	Without
Light block supply	Without supply
Contacts type and composition	2 NO + 2 NC
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

Environment

Product certifications	NEMA CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	163.293 g
Package 1 Height	29.032 cm

Package 1 width	11.43 cm
Package 1 Length	73.742 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov