

Product data sheet

Specifications



PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS

9001SK1L1A

Main

Range of product	Harmony 9001SK
Product or component type	Push-button
Device short name	9001SK

Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Contacts type and composition	Without contact block
Contact operation	Standard
Mechanical durability	5000000 cycles
Device presentation	Basic element

Environment

Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 JIS C 852 JIS C 4520 EN/IEC 60947-5-4 EN/IEC 60947-1 UL 508
IP degree of protection	IP66
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	181.437 g
Package 1 Height	12.903 cm
Package 1 width	5.08 cm
Package 1 Length	32.774 cm

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov