

Product data sheet

Specifications



PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS

9001SKR9GH13

Main

Range of product	Harmony 9001SK
Product or component type	Mushroom head push-button
Device short name	9001SK
Type of operator	spring return
Operator profile	Green mushroom Ø 41 mm
Operator additional information	Screw-on plastic mushroom

Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Contacts type and composition	1 C/O
Contact operation	Standard
Mechanical durability	5000000 cycles
Device presentation	Complete product

Environment

Standards	UL 508 EN/IEC 60947-5-4 JIS C 4520 EN/IEC 60947-1 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-1
IP degree of protection	IP66
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	226.796 g
Package 1 Height	12.903 cm
Package 1 width	5.08 cm
Package 1 Length	32.774 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov