

8501CO7V24

Power Relay, Type C, 2 HP, 30A resistive at 300 VAC, DPST, 2 normally open contacts, 240 VAC coil



Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Power Relay 8501C
Product or Component Type	Power relay
Device short name	Type C
Line Rated Current	30 A
Device Application	Suited for controlling small single phase motors and other light loads
Switch Function	DPST
Contacts type and composition	2 NO
[Uc] control circuit voltage	240 V AC 50/60 Hz
Rated power in hp	2.0 Hp
Maximum switching voltage	600 V AC

Complementary

Catalog class	8501
Phase	1 phase
Connections - Terminals	Screw clamp terminal
AWG gauge	AWG 10 copper
Tightening torque	11...15 Lbf.In (1.24...1.69 N.m)
Hold-in power consumption in VA	10 VA
Mounting Support	Panel mounting

Environment

Ambient Air Temperature for Operation	-22...122 °F (-30...50 °C)
Product Certifications	UL listed file E78351 CCN NLDX CSA CE
Height	2.43 In (61.72 mm)
Width	2.5 In (63.50 mm)
Depth	2.25 In (57.15 mm)

Ordering and shipping details

Category	21131 - 8501 C
Discount Schedule	CP2
GTIN	785901052074
Nbr. of units in pkg.	1
Package weight(Lbs)	9.60 Oz (272.155 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.30 In (5.842 cm)
Package 1 width	2.60 In (6.604 cm)
Package 1 Length	2.50 In (6.35 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**