

1825289-5 ✓ ACTIVE

Alcoswitch | Alcoswitch MHS

TE Internal #: 1825289-5

Alcoswitch MHS, Slide Switches, Double Pole - Double Throw Configuration (Pole-Throw), Vertical, Copper Alloy, Single Actuator, 2 Position

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > Slide Switches



Configuration (Pole-Throw): **Double Pole - Double Throw**

Slide Switch Mounting Angle: **Vertical**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Number of Slide Switch Positions: **2**

Features

Product Type Features

Threaded Case	Without
Grade	Instrumentation
Switch Type	Slide
Product Type	Switch
Switch Style	Low Profile
Terminal Configuration	Standard
Actuator Style	Lever

Configuration Features

Terminals Connected	5-4, 2-1
Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Number of Slide Switch Positions	2
Operating Function	On Off On

Electrical Characteristics

Slide Switch Voltage Rating (VAC)	125
-----------------------------------	-----

Body Features

Actuator Travel	2 mm[.079 in]
Actuator Material	Thermoplastic



Actuator Color	Black
----------------	-------

Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------

Slide Switch Contact Current Rating	.3 A
-------------------------------------	------

Switch Contact Plating Material	Silver
---------------------------------	--------

Termination Features

Termination Type	PC
------------------	----

Mechanical Attachment

PCB Mount Retention	With
---------------------	------

PCB Mount Retention Type	Guide Post
--------------------------	------------

Slide Switch Mounting Angle	Vertical
-----------------------------	----------

Slide Switch Mounting Type	Through Hole
----------------------------	--------------

Dimensions

PCB Tail Length	3.51 mm[.138 in]
-----------------	------------------

Actuator Length	4.5 mm[.18 in]
-----------------	----------------

Width	6.2 mm[.244 in]
-------	-----------------

Length	15 mm[.591 in]
--------	----------------

Industry Standards

UL Flammability Rating	UL 94-HB
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per
-----------------	--

homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1825289-1
MHS22204=DPDT SL SW VERT AG



TE Part # 1825289-8
MHS23304=DP3T SL SW VERT AG



TE Part # 1825289-2
MHS222G04=DPDT SL SW VERT AU



TE Part # 1-1825289-0
MHS233K04=DP3T SL SW VERT AG




TE Part # 1825289-9
MHS233G04=DP3T SL SW VERT AU

Also in the Series | Alcoswitch MHS



Slide Switches(16)

Customers Also Bought



Documents

Product Drawings

[MHS22304=DPDT SL SW VERT AG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1825289-5_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825289-5_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825289-5_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English