

2299501-1 ✓ ACTIVE

TE Internal #: CR2101-000

TE Internal Description: WINGGRIP WC, BLUE, 22-14 AWG

[View on TE.com >](#)



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1775469-2
HPI CONN., 2.0MM, R/A, SMT, 2P,
80U"



TE Part #CR2103-000
CPGI-WC-WG-OR-BULK



TE Part #1445336-1
LOOSE PC CONTACT TIN PLATED



TE Part #CR2105-000
CPGI-WC-WG-YW-BULK



TE Part #CR2102-000
CPGI-WC-WG-GR-BULK



TE Part #2337019-1
UMCC Micro-Coax receptacle, Gen 1



TE Part #2199230-4
M.2 0.5PITCH 4.2H KEY E 15U" AU"



TE Part #CR2104-000
CPGI-WC-WG-RD-BULK



TE Part #1437565-3
FSM101=12MM FSM TYPE WITH RAIS



TE Part #CR2106-000
CPGI-WC-WNG-BL-BULK

Documents

Product Drawings

WINGGRIP WC, BLUE, 22-14 AWG

English

Datasheets & Catalog Pages

Twist Splice Wire Connectors flyer

English

Twist Splice wire connectors