

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638192400](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Hand Crimp Tool for 2.00mm Pitch Wire-to-Board Crimp Terminals, 26-28 AWG Wire

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	883906191221
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 317.100/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
 ATS-638192400-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

iGrid Wire-to-Board Crimp Terminal [501648](#)

**Application Tooling Description** | **FAQ Product #**

2.00mm Pitch, iGrid Female Crimp Terminal, Female, Tin (Sn) Plating, 26-28 AWG, Reel	<a href="#">5016481000</a>
2.00mm Pitch, iGrid Female Crimp Terminal, 0.10µm Gold (Au) Plating, 26-26 AWG, Reel	<a href="#">5030952200</a>
2.00mm Pitch, iGrid Female Crimp Terminal, 0.38µm Gold (Au) Plating, 26-26 AWG, Reel	<a href="#">5030953200</a>
2.00mm Pitch, iGrid Female Crimp	<a href="#">5030954200</a>

Terminal, 0.76µm  
Gold (Au) Plating,  
26-26 AWG, Reel

This document was generated on 11/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**