

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638233700](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for ISO (M3) Receptacle Terminals


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	884982769861
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents [ATS-6382337HM-001](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129](#) Series

Use With

[638233770](#) Modular Crimp Head, [33001](#), [33012](#), [34750](#), [34780](#) MX150 ISO (M3) Receptacle Terminals for 0.35mm² and 0.50mm² ISO Wires

Application Tooling Description

FAQ Product #

MX150 Female [330012006](#)

Terminal for Mat-Sealed Connectors, Gold Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm², Right Reel Payoff

MX150 Female [330013006](#)

Terminal for Mat-Sealed Connectors, Gold Plating, Grip Code M3, Preferred

Terminal for use in Sealed Application with 0.35-0.50mm ² , Left Reel Payoff MX150 Female	<u>330014005</u>
Terminal for Mat-Sealed Connectors, Silver Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm ² , Right Reel Payoff MX150 Female	<u>330015005</u>
Terminal for Mat-Sealed Connectors, Silver Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm ² , Left Reel Payoff MX150 Female	<u>330122004</u>
Terminal for Mat-Sealed Connectors, Tin Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm ² , Right Reel Payoff, Contact Material Thickness 0.30mm ² MX150 Female	<u>330123004</u>
Terminal for Mat-Sealed Connectors, Tin Plating, Grip Code M3, Preferred	
Terminal for use in Sealed Application with 0.35-0.50mm ² , Left Reel Payoff, Contact Material Thickness 0.30mm ²	

This document was generated on 11/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION