

Ampli-Set

Kompakt-Sortiment für Service und Reparaturen

Best.-Nr. **725972-0**

Handlich, praktisch, leicht; ausgestattet mit der Präzisions-Crimpzange SUPER-CHAMP und 21 verschiedenen lötfreien Anschlußelementen – das ist Ampli-Set.

Die reichhaltige Bestückung erlaubt problemlose und schnelle Durchführung aller gängigen Service- und Reparaturarbeiten.

Anschlüsselemente und Handzange sind in fünf getrennten, glasklaren Kunststofftaschen untergebracht. Zwei stabile Druckknöpfe schließen das Ampli-Set zu einer handlichen, kleinen Packung zusammen. Für die Befestigung an der Wand sind zwei separate Ausparungen vorhanden.



Ampli-Set

Compact assortment for service and repair

Part No. **725972-0**

The Ampli-Set is handy, practical, light weight, equipped with the precision crimp tool SUPER-CHAMP and 21 various solderless connectors.

The wide variety of parts allows quick and easy completion of all service and repair work.

Connectors and hand tool are in 5 separate clear plastic pouches. 2 stable snaps are used to close the Ampli-Set into a hand sized package. 2 separate holes are provided for hanging on the wall.

Lfd.-Nr. No.	Beschreibung Description	Stückzahl Number	Best.-Nr. Part No.
1	PG Stoßverbinder 0,4–1,0 mm ² /PG Butt Splices 0.4–1.0 mm ²	7	34070
2	PG Ringzunge 0,4–1,0 mm ² ; M 3–3,5/PG Ring Tongue 0.4–1.0 mm ² ; M 3–3.5	3	34142
3	PG Ringzunge 0,4–1,0 mm ² ; M 5/PG Ring Tongue 0.4–1.0 mm ² ; M 5	3	130014
4	PG Gabel 0,4–1,0 mm ² ; M 2,6/PG Spade 0.4–1.0 mm ² ; M 2.6	3	165004
5	PG Stiftkabelschuh 0,4–1,0 mm ² ; kurz/PG Wire Pin 0.4–1.0 mm ² ; short	3	165143
6	PG Stiftkabelschuh 0,4–1,0 mm ² ; lang/PG Wire Pin 0.4–1.0 mm ² ; long	2	165167
7	PG Stoßverbinder 1,1–2,6 mm ² /PG Butt Splice 1.1–2.6 mm ²	5	34071
8	PG Ringzunge 1,1–2,6 mm ² ; M 5/PG Ring Tongue 1.1–2.6 mm ² ; M 5	3	130102
9	PG Gabel 1,1–2,6 mm ² ; M 4/PG Spade 1.1–2.6 mm ² ; M 4	2	34166
10	PG Stiftkabelschuh 1,1–2,6 mm ² /PG Wire Pin 1.1–2.6 mm ²	2	165171
11	PG Ringzunge 2,7–6,6 mm ² ; M 6/PG Ring Tongue 2.7–6.6 mm ² ; M 6	2	165035
12	PG Ringzunge 2,7–6,6 mm ² ; M 8/PG Ring Tongue 2.7–6.6 mm ² ; M 8	1	160296
13	PG Gabel 2,7–6,6 mm ² ; M 5/PG Spade 2.7–6.6 mm ² ; M 5	1	165017
14	PG Stiftkabelschuh 2,7–6,6 mm ² /PG Wire Pin 2.7–6.6 mm ²	1	165085
15	Nylon-Endverbinder 1,5–6,6 mm ² /Nylon End Splice 1.5–6.6 mm ²	3	324067
16	PIDG-FASTON Steckhülse 6,3 x 0,8; 0,4–1,0 mm ² PIDG-FASTON Receptacle 6.3 x 0.8; 0.4–1.0 mm ²	3	9-160583-2
17	PIDG-FASTON Steckhülse 6,3 x 0,8; 1,1–2,6 mm ² PIDG-FASTON Receptacle 6.3 x 0.8; 1.1–2.6 mm ²	2	9-160313-2
18	Vollisolierte FASTON Steckhülse für Flachstecker 6,3 x 0,8; 1,1–2,6 mm ² Insulated FASTON Receptacle for Tab 6.3 x 0.8; 1.1–2.6 mm ²	2	735159
19	PIDG-FASTON Steckhülse mit Abzweig 6,3 x 0,8; 1,1–2,6 mm ² PIDG-FASTON Piggy Back Receptacle 6.3 x 0.8; 1.1–2.6 mm ²	2	9-160463-2
20	PIDG-FASTON Steckhülse 6,3 x 0,8; 2,7–6,6 mm ² PIDG-FASTON Receptacle 6.3 x 0.8; 2.7–6.6 mm ²	1	160314-2
21	SUPER-CHAMP Handzange/SUPER-CHAMP Hand Tool	1	169060-8