


ISO 1:1

Retainer for cable tie /  
Aufnahme fuer Kabelbinder  
(8 x 2.75 mm)



Printed copy for information only/  
Ausdruck nur zur Information

Specification:

- Performance requirements at equilibrium condition standard atmosphere 23 °C / 50% RH
- Tolerances dimension without tolerances details to: DIN 16742 - TG6
- Material: PA66+PA6 heatstabilized impact modified
- Material color: black
- Panel thickness/ - Blechdicke:

The manufacturing-related geometry changes (injection point, ejectors marks, etc.) allowed. Design of the details are left to suppliers discretion.

Spezifikation:

- Leistungsanforderung im Gleichgewichtszustand Normalklima 23 °C / 50% RH
- Toleranzen Masse ohne Toleranzangabe nach: DIN 16742 - TG6
- Material: PA66+PA6 hitzestabilisiert schlagzaeh modifiziert
- Material Farbe: schwarz
- Material Dicke: 4,5 mm

Durch das Herstellverfahren bedingte Geometrieaenderungen (Anspritzung, Auswerfermarkierungen, etc.) zulaessig. Einzelheiten der Ausfuehrung bleiben dem Hersteller ueberlassen.

Revision Level		
Drawing	State	Part
00.0	Design Release	-
Changed	Date (YYYY/MM/DD)	
-	-	
Approved	Date (YYYY/MM/DD)	
-	-	

Revision Record	

All drawing revisions are stored in CAD PDM database

The copyright of this drawing is reserved by HellermannTyton.

Drawn	Date (YYYY/MM/DD)
C.Cordts	2020.02.18
Approved	Date (YYYY/MM/DD)
M.Maschmann	2020.02.18

Title	Scale
ACFM5W8PT4.5	1:1; 2:1
Drawing-No	Global Project Number
19-0075-001-CSG	19-0075
Sheet	Format
1 / 1	A3