
MCMAUDIO SELECT"

Model Number:	55-2974			
GENERAL SPECIFICATIONS				
Nominal Diameter:	15 inch			
Rated Lmpedance:	8 ohms			
Operating Bandwidth:	50–3k hz (–3dB)			
Power Handling Capacity:	200 Watts			
Sensitivity (1W/M):	92 dB(+-3dB)			
Voice Coil Diameter:	2 inch			
THIELE-SMALL PARAMRTERS				
Resonance Frequency	Fs:	32.5 HZ		
DC Resistance	Re:	7.2 ohm		
Mechanical Q Factor	Qms:	3.0845		
Electrical Q Factor	Qes:	0.5591		
Total Q Factor	Qts:	0.4733		
Equivalent Cas air load	Vas:	322.23 L		
Surface Area of Cone	Sd:	0.0840 m2		
Efficiency Bandwidth Product	EBP	58		
Voice Coil Over Hang	X-max	ax6 mm		
Voice Coil Inductance	Le	1.522mH		
PHYSICAL INFORMATION				
Basket:	Pressed steel chassis			
Magnet Type:	40 OZ			
Cone Material:	PP			
Surround:	Rubber			
Dust Cap:	РР			
Damper:	cloth			


SPEAKER SPECIFICATIONS




Date: 2010/6/28


	Sealed Box			
			Vented Box	
Suggested spaleser peremeters	Sealed		Vented	
Suggested encloser parameters	Small	Large	Small	Large
Enclosure volume, cu. ft.	0.74	NA	0.74	NA
Vent length, inches	-	-	4.1	-
Vent diameter, inches	-	-	2	-
Enclosure Frequency, Hz	59	-	-	-
Fb Tuning Frequency of vented Enclosure, Hz	NA	-	44	-
F3 Systems 3dB Down Point (sealed), Hz	44	-	-	-


Impedance Curve



Response Curve







55-2974