


## 183A.20CPE | 183A-183AE.CPE - Half-round long snipe-nose pliers



### Description:

- Extra Narrow, finely serrated tips - 183A: 40° angled tip and side cutting edges. - 183AE: straight long thin nose with wire stripping & gripping 1.5mm<sup>2</sup> - 2.5mm<sup>2</sup> - 4mm<sup>2</sup>.
- Cutting edges for copper and hard steel wire to maximum specification of 1.6mm 160 kg/mm<sup>2</sup>.
- High durability Carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal length)
- Chrome finish for corrosion resistance

	183A.20CPE
Length L [mm]	200.0
Thickness E [mm]	3.0
Thickness E1 [mm]	18.0
Head Height C [mm]	69.0
Weight [g]	185.0
Length L1 [mm]	2.5