


190A.16CPE | 190A.CPE - High-performance end cutters



Description:

- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 190A.16CPE : 2.0mm 210 kg/mm² - 190A.20CPE : 2.5mm 200 kg/mm²
- High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.
- High durability carbon alloy steel, with induction hardened cutting edges.
- Bi-Material ergonomic grips resistant to chemical agents featuring: - Return spring - Tether ready point (Tether point adds 10mm to nominal length)
- Chrome finish for corrosion resistance

	190A.16CPE
A [mm]	6.5
Head Width B [mm]	28.0
Head Height C [mm]	6.5
Diameter D Maxi [mm]	2.0
Thickness E [mm]	11.5
Length L [mm]	160.0

Weight [g]

200.0