

E.306A30R | E.306A - Electronic torque wrenches with ratchet




Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Accuracy: $\pm 2\%$ between 20% and 100% wrench capacity.
- Measuring mode: peak or follower.
- Measuring unit: N.m, lbf.ft, lbf.in and kg.cm.
- Bits: 9 x 12 and 14 x 18 mm.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Presetting possible of 9 torque and/or angle values.
- Memory 250 values with PC USB link.
- Supplied in plastic case with foam interior.

	E.306A30R
Capacity [Nm]	1.5 - 30
Square [in]	1/4
Weight [Kg]	1.6
Ratchet ["]	R.372