PRECISION STRAIN GAGE

ROSETTE STRAIN GAGES 0/45/90° AND 0/60/120°

RECTANGULAR AND DELTA, 3 ELEMENT

OMEGA® offers planar and stacked rosettes. Planar rosettes have all 3 strain gage elements in one plane. Stacked rosettes have the 3 strain gage elements stacked one on top of the other. Consider the difference when you make your strain gage selection. Planar rosettes have some advantages over

stacked rosettes. Planar rosettes tend to be thinner and more flexible. They can be used on curved surfaces and conform better to the irregular surfaces. Reinforcement effects of planar gages are minimized. Planar rosettes have superior heat dissipation capability, and better stability. Stacked rosettes are

Custom-Designed
Strain Gages
Available!
No Minimum Quantities.
Consult Engineering.

thicker and stiffer because you have the multiple layers stacked on top of one another. They do not disperse heat as well when voltage is applied to them.

To Order											
	MODEL NO. Pkg of 5	NOM.	DIMENSIONS mm (inch)†					Vis		sit us online	
GAGE PATTERN Leads not shown		RESIS- TANCE (Ω)	GRID		CARRIER						
			A	В	С	D	MAX V* (Vrms)	TERMINATION	TEMP COMP	TERM PAD	
0/45/90° RECTANGULAR 3 ELEMENT											
Shown actual size, 16 mm	SGD-3/120-RY11	120	3.00 (0.118)	2.90 (0.114)	16.00 (0.630)	16.00 (0.630)	5.5	Ribbon Leads	ST		
	SGD-3/120-RY13	120	Three-element 45° rectangular planar rosette 120 Ω				8	Ribbon Leads	AL		
	SGD-3/120-RY31	120					5.5	Solder Pads	ST	BPT-3	
	SGD-3/120-RY33	120					8	Solder Pads	AL		
Shown actual size, 16 mm	SGD-3/350-RY11	350	3.00 (0.118)	2.90 (0.114)	16.00 (0.630)	16.00 (0.630)	9.5	Ribbon Leads	ST		
	SGD-3/350-RY13	350		mont 45°	13	Ribbon Leads	AL				
	SGD-3/350-RY31	350	Three-element 45° rectangular planar rosette 350 Ω			9.5	Solder Pads	ST	BPT-3		
	SGD-3/350-RY33	350				13	Solder Pads	AL			

To Order DIMENSIONS mm (inch)† Visit us only										
			GRID		CARRIER					-3 Onl
GAGE PATTERN Leads not shown	MODEL NO. Pkg of 5	TANCE (Ω)	A	В	С	D	MAX V* (Vrms)	TERMINATION	TEMP COMP	TERM PAD
0/60/120° DEL	TA 3-ELEMENT									
Shown actual size, 16 mm	SGD-3/120-RY41	120	3.00 (0.118)	2.90 (0.114)	16.00 (0.630)	16.00 (0.630)	5.5	Ribbon Leads	ST	
	SGD-3/120-RY43	120	Three-element 60° delta planar rosette 120 Ω				8	Ribbon Leads	AL	BPT-3
	SGD-3/120-RY71	120					5.5	Solder Pads	ST	
	SGD-3/120-RY73	120					8	Solder Pads	AL	
Shown actual size, 16 mm	SGD-3/350-RY41	350	3.00 (0.118)	2.90 (0.114)	16.00 (0.630)	16.00 (0.630)	9.5	Ribbon Leads	ST	
	SGD-3/350-RY43	350	Three-element 60° delta planar rosette 350 Ω			13	Ribbon Leads	AL	BPT-3	
	SGD-3/350-RY71	350				9.5	Solder Pads	ST		
	SGD-3/350-RY73	350				13	Solder Pads	AL		

DISCOUNT	SCHEDULE
o 10 pkac	No

50 and up and OEM . .Consult Factory

† For dimensions key, visit us online.

* Maximum permitted bridge energizing voltage (Vrms).

Note: For strain gage accessories visit us online.

Ordering Example: SGD-3/350-RY33, 350 Ω nominal-resistance strain gage.

