

www.vishay.com

Vishay General Semiconductor

AUTOMOTIVE

RoHS

COMPLIANT

HALOGEN FREE

Surface-Mount Glass Passivated Rectifier



SMC (DO-214AB)

Cathode O Anode

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS							
I _{F(AV)}	5.0 A						
V _{RRM}	50 V, 100 V, 200 V, 400 V, 600 V 800 V, 1000 V						
I _{FSM}	100 A						
I _R	10 μA						
V _F	1.15 V						
T _J max.	150 °C						
Package	SMC (DO-214AB)						
Circuit configuration	Single						

FEATURES

- Low profile package
- · Ideal for automated placement
- · Glass passivated pellet chip junction
- · Low forward voltage drop
- Low leakage current
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 - Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, automotive and telecommunication.

MECHANICAL DATA

Case: SMC (DO-214AB)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - halogen-free, RoHS-compliant, commercial

grade

Base P/NHE3_X - RoHS-compliant and AEC-Q101 qualified ("_X" denotes revision code e.g. A, B,.....)

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, and HE3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	S5A	S5B	S5D	S5G	S5J	S5K	S5M	UNIT
Device marking code		5A	5B	5D	5G	5J	5K	5M	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at $T_L = 75$ °C	I _{F(AV)}	5.0					Α		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	100					Α		
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +150					°C		

S5A, S5B, S5D, S5G, S5J, S5K, S5M

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS	TEST CONDITIONS SYMBOL S5A S5B S			S5D	S5G	S5J	S5K	S5M	UNIT
Maximum instantaneous forward voltage	5.0 A	V _F	1.15				1.15			V
Maximum DC reverse current at	T _A = 25 °C	lo.	10							μA
rated DC blocking voltage	T _A = 125 °C	- I _R	250							μΛ
Typical reverse recovery time	$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A},$ $I_{rr} = 0.25 \text{ A}$	t _{rr}	2.5				μs			
Typical junction capacitance	4.0 V, 1 MHz	CJ	40					pF		

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL S5A S5B S5D S5G S5J S5K S5M UNIT					
Typical thermal resistance (1)	$R_{\theta JL}$	10 °C/\				°C/W

Note

⁽¹⁾ Thermal resistance from junction to lead mounted on PCB with 0.3" x 0.3" (8.0 mm x 8.0 mm) copper pad area

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
S5J-E3/57T	0.211	57T	850	7" diameter plastic tape and reel					
S5J-E3/9AT	0.211	9AT	3500	13" diameter plastic tape and reel					
S5J-M3/57T	0.211	57T	850	7" diameter plastic tape and reel					
S5J-M3/9AT	0.211	9AT	3500	13" diameter plastic tape and reel					
S5JHE3_A/H (1)	0.211	Н	850	7" diameter plastic tape and reel					
S5JHE3_A/I (1)	0.211	I	3500	13" diameter plastic tape and reel					

Note

⁽¹⁾ AEC-Q101 qualified

www.vishay.com Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current





Fig. 3 - Typical Instantaneous Forward Characteristics








Fig. 5 - Typical Junction Capacitance




www.vishay.com

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

O.126 (3.20) 0.114 (2.90) 0.280 (7.11) 0.260 (6.60) 0.006 (1.52) 0.006 (1.52) 0.030 (0.76) 0.320 (8.13) 0.305 (7.75)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.