## **190A.16VE** | 1,000 Volt insulated high-performance end cutters



## **Description:**

• Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 190A.16VE: 2.0mm 210 kg/mm<sup>2</sup>

• High mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.

• High durability Carbon alloy steel, with induction hardened cutting edges.

• Bi-Material ergonomic grips resistant to chemical agents. - Positive return spring - Tether ready tether point (Tether point adds 10mm to nominal length)

<b>=</b> 0	190A.16VE
A [mm]	6.5
Length L [mm]	160.0
Thickness E [mm]	11.5
Head Height C [mm]	6.5
Head Width B [mm]	28.0
Height H [mm]	23.0