

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [08020SA-12K-AA-00](#)[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

## DC Axial Fans - 08020SA-12K-AA-00

[Get a sample](#)

### Resources

<a href="#">Specification Sheet</a>	<a href="#">Series Data Sheet</a>
<a href="#">Certificates</a>	<a href="#">RoHS Certificate</a>



←











→

Specifications

Category	DC Axial Fans
Part Number	08020SA-12K-AA-00
Frame Width [mm]	80
Frame Height [mm]	80
Frame Depth [mm]	20

<b>Max. Air Flow [CFM]</b>	31.1
<b>Max. Air Flow [m3 per min]</b>	0.88
<b>Max. Static Pressure [In H2O]</b>	0.14
<b>Max. Static Pressure [Pa]</b>	34.9
<b>Fan Speed [RPM]</b>	2900
<b>Noise [dB]</b>	31
<b>Life Expectancy [L10]</b>	60 degree C 40,000 Hours
<b>Bearing Type</b>	Ball Bearing
<b>Nominal Voltage [V]</b>	12
<b>Operating Voltage - Lower [V]</b>	6
<b>Operating Voltage - Upper [V]</b>	13.8
<b>Current [A]</b>	0.07

<b>Input Power [W]</b>	0.8
<b>Mass [g]</b>	80
<b>Tach / Locked Rotor Output</b>	No
<b>Status</b>	Active

**PRODUCTS**[See All Products](#) →[Find A Distributor](#)[Find a Sales Representative](#)**INDUSTRIES**[See All Industries](#)[Automotive](#)[Industrial](#)[Medical](#)[Consumer Technology](#)[Smart City](#)[Lighting Innovations](#)**RESOURCES**[See All Resources](#) →[Application Notes & Whitepapers](#)[Latest News](#)[Videos](#)**CONTACT****NMB Technologies Corporation****(248) 919-2250****[info@nmbtc.com](mailto:info@nmbtc.com)**

## Have A Question?

**Our precision component experts can help you find the right solutions.**

[Contact Us Today](#)[Find A Distributor](#)[Find Sales Rep For Fans](#) →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)[Careers](#)[Sitemap](#)[Privacy Policy](#)[Terms of use](#)

