

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [08020SA-12J-AL-00](#)[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 08020SA-12J-AL-00

[Get a sample](#)

Resources

Specification Sheet	Series Data Sheet
Certificates	RoHS Certificate



Specifications

Category	DC Axial Fans
Part Number	08020SA-12J-AL-00
Frame Width [mm]	80
Frame Height [mm]	80
Frame Depth [mm]	20

Max. Air Flow [CFM]	27.5
Max. Air Flow [m3 per min]	0.78
Max. Static Pressure [In H2O]	0.11
Max. Static Pressure [Pa]	28.3
Fan Speed [RPM]	2600
Noise [dB]	27
Life Expectancy [L10]	60 degree C 40,000 Hours
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	6
Operating Voltage - Upper [V]	13.8
Current [A]	0.05

Input Power [W]	0.6
Mass [g]	80
Tach / Locked Rotor Output	Locked Rotor
Status	Active

PRODUCTS

[See All Products](#) →

[Find A Distributor](#)

[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#)

[Automotive](#)

[Industrial](#)

[Medical](#)

[Consumer Technology](#)

[Smart City](#)

[Lighting Innovations](#)

RESOURCES

→ [See All Resources](#) →

[Application Notes & Whitepapers](#)

[Latest News](#)

[Videos](#)

CONTACT

NMB Technologies Corporation

[\(248\) 919-2250](#)

info@nmbtc.com

Have A Question?

Our precision component experts can help you find the right solutions.

[Contact Us Today](#)

[Find A Distributor](#)

[Find Sales Rep For Fans](#) →

