

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > 09225SA-12N-AL-D0[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 09225SA-12N-AL-D0

[Get a sample](#)

Resources

Specification Sheet	Series Data Sheet
Certificates	RoHS Certificate
CAD Files	09225SA.stp
CAD Files	09225SA.sldprt



CAD Files	09225SA.prt
CAD Files	09225SA.iges

Specifications

Category	DC Axial Fans
Part Number	09225SA-12N-AL-D0
Frame Width [mm]	92
Frame Height [mm]	92
Frame Depth [mm]	25
Max. Air Flow [CFM]	51.2
Max. Air Flow [m3 per min]	1.45
Max. Static Pressure [In H2O]	0.18

Max. Static Pressure [Pa]	45
Fan Speed [RPM]	3100
Noise [dB]	32
Life Expectancy [L10]	40,000 hours at 60C
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	6
Operating Voltage - Upper [V]	13.8
Current [A]	0.16
Input Power [W]	1.92
Mass [g]	102
Tach / Locked Rotor Output	Locked Rotor

Status

Active

PRODUCTS

[See All Products](#) →
[Find A Distributor](#)
[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#) →
[Automotive](#)
[Industrial](#)
[Medical](#)
[Consumer Technology](#)
[Smart City](#)
[Lighting Innovations](#)

RESOURCES

[See All Resources](#) →
[Application Notes & Whitepapers](#)
[Latest News](#)
[Videos](#)

CONTACT

NMB Technologies Corporation
[\(248\) 919-2250](#)
info@nmbtc.com

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

Find Sales Rep For Fans →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)

[Careers](#)

[Sitemap](#)

[Privacy Policy](#)

[Terms of use](#)