

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > 08020SA-12L-AA-00[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 08020SA-12L-AA-00

[Get a sample](#)

Resources

Specification Sheet	Series Data Sheet
Certificates	RoHS Certificate



Specifications

Category	DC Axial Fans
Part Number	08020SA-12L-AA-00
Frame Width [mm]	80
Frame Height [mm]	80
Frame Depth [mm]	20

Max. Air Flow [CFM]	36
Max. Air Flow [m3 per min]	1.02
Max. Static Pressure [In H2O]	0.17
Max. Static Pressure [Pa]	43.6
Fan Speed [RPM]	3300
Noise [dB]	34
Life Expectancy [L10]	60 degree C 40,000 Hours
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	6
Operating Voltage - Upper [V]	13.8
Current [A]	0.09

Input Power [W]	1.1
Mass [g]	80
Tach / Locked Rotor Output	No
Status	Active

PRODUCTS[See All Products](#) →[Find A Distributor](#)[Find a Sales
Representative](#)**INDUSTRIES**[See All
Industries](#)[Automotive](#)[Industrial](#)[Medical](#)[Consumer
Technology](#)[Smart City](#)[Lighting
Innovations](#)**RESOURCES**[See All Resources](#) →[Application Notes &
Whitepapers](#)[Latest News](#)[Videos](#)**CONTACT****NMB Technologies
Corporation****(248) 919-2250****info@nmbtc.com**

Have A Question?

**Our precision component experts can help you
find the right solutions.**

[Contact Us Today](#)[Find A Distributor](#)[Find Sales Rep For Fans](#) →

NMB Technologies Corporation © 2021. All Rights
Reserved.

[Company](#)[Careers](#)[Sitemap](#)[Privacy
Policy](#)[Terms of
use](#)

