

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [06020SA-12J-AL-00](#)[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

## DC Axial Fans - 06020SA-12J-AL-00

[Get a sample](#)

### Resources

<a href="#">Specification Sheet</a>	<a href="#">Series Data Sheet</a>
<a href="#">Certificates</a>	<a href="#">RoHS Certificate</a>



Specifications

Category	DC Axial Fans
Part Number	06020SA-12J-AL-00
Frame Width [mm]	60
Frame Height [mm]	60
Frame Depth [mm]	20

<b>Max. Air Flow [CFM]</b>	12.7
<b>Max. Air Flow [m3 per min]</b>	0.356
<b>Max. Static Pressure [In H2O]</b>	0.09
<b>Max. Static Pressure [Pa]</b>	22.4
<b>Fan Speed [RPM]</b>	2800
<b>Noise [dB]</b>	21.5
<b>Life Expectancy [L10]</b>	60 degree C 40,000 Hours AA/EA
<b>Bearing Type</b>	Ball Bearing
<b>Operating Voltage - Lower [V]</b>	6
<b>Operating Voltage - Upper [V]</b>	13.8
<b>Input Power [W]</b>	0.6
<b>Tach / Locked Rotor Output</b>	Locked Rotor

Status

Active

PRODUCTS

[See All Products](#) →  
[Find A Distributor](#)  
[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#) →  
[Automotive](#)  
[Industrial](#)  
[Medical](#)  
[Consumer Technology](#)  
[Smart City](#)  
[Lighting Innovations](#)

RESOURCES

[See All Resources](#) →  
[Application Notes & Whitepapers](#)  
[Latest News](#)  
[Videos](#)

CONTACT

NMB Technologies Corporation  
[\(248\) 919-2250](#)  
[info@nmbtc.com](mailto:info@nmbtc.com)

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

[Find Sales Rep For Fans](#) →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)

[Careers](#)

[Sitemap](#)

[Privacy Policy](#)

[Terms of use](#)