

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > 09225SA-12M-AT-D0[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

## DC Axial Fans - 09225SA-12M-AT-D0

[Get a sample](#)

### Resources

<a href="#">Specification Sheet</a>	<a href="#">Series Data Sheet</a>
<a href="#">Certificates</a>	<a href="#">RoHS Certificate</a>
<a href="#">CAD Files</a>	<a href="#">09225SA.stp</a>
<a href="#">CAD Files</a>	<a href="#">09225SA.sldprt</a>



CAD Files	<a href="#">09225SA.prt</a>
CAD Files	<a href="#">09225SA.iges</a>

Specifications

Category	DC Axial Fans
Part Number	09225SA-12M-AT-D0
Frame Width [mm]	92
Frame Height [mm]	92
Frame Depth [mm]	25
Max. Air Flow [CFM]	45.2
Max. Air Flow [m3 per min]	1.28
Max. Static Pressure [In H2O]	0.145

Max. Static Pressure [Pa]	36.2
Fan Speed [RPM]	2750
Noise [dB]	29
Life Expectancy [L10]	40,000 hours at 60C
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	6
Operating Voltage - Upper [V]	13.8
Current [A]	0.14
Input Power [W]	1.68
Mass [g]	102
Tach / Locked Rotor Output	Tach Output

Status

Active

PRODUCTS

[See All Products](#) →  
[Find A Distributor](#)  
[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#) →  
[Automotive](#)  
[Industrial](#)  
[Medical](#)  
[Consumer Technology](#)  
[Smart City](#)  
[Lighting Innovations](#)

RESOURCES

[See All Resources](#) →  
[Application Notes & Whitepapers](#)  
[Latest News](#)  
[Videos](#)

CONTACT

NMB Technologies Corporation  
[\(248\) 919-2250](#)  
[info@nmbtc.com](mailto:info@nmbtc.com)

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

[Find Sales Rep For Fans](#) →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)

[Careers](#)

[Sitemap](#)

[Privacy Policy](#)

[Terms of use](#)