

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > 09225SA-12P-EL-D0[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 09225SA-12P-EL-D0

[Get a sample](#)

Resources

Specification Sheet	Series Data Sheet
Certificates	RoHS Certificate
CAD Files	09225SA.stp
CAD Files	09225SA.sldprt



CAD Files	09225SA.prt
CAD Files	09225SA.iges

Specifications

Category	DC Axial Fans
Part Number	09225SA-12P-EL-D0
Frame Width [mm]	92
Frame Height [mm]	92
Frame Depth [mm]	25
Max. Air Flow [CFM]	58.97
Max. Air Flow [m3 per min]	1.67
Max. Static Pressure [In H2O]	0.216

Max. Static Pressure [Pa]	53.9
Fan Speed [RPM]	3550
Noise [dB]	37
Life Expectancy [L10]	40,000 hours at 60C
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	7
Operating Voltage - Upper [V]	13.8
Current [A]	0.19
Input Power [W]	2.28
Mass [g]	102
Tach / Locked Rotor Output	Locked Rotor

Status

Active

PRODUCTS

[See All Products](#) →

[Find A Distributor](#)

[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#)

[Automotive](#)

[Industrial](#)

[Medical](#)

[Consumer Technology](#)

[Smart City](#)

[Lighting Innovations](#)

RESOURCES

[See All Resources](#) →

[Application Notes & Whitepapers](#)

[Latest News](#)

[Videos](#)

CONTACT

NMB Technologies Corporation

[\(248\) 919-2250](#)

info@nmbtc.com

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

Find Sales Rep For Fans →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)

[Careers](#)

[Sitemap](#)

[Privacy Policy](#)

[Terms of use](#)