

Update related to COVID-19. Learn More →



Products

Industries

About

Resources

Blog

Contact us

Find A Distributor

Home > Products > Cooling Fans > DC Axial Fans > 15050VA-24N-EL-00

← Back To DC Axial Fans

Have a question about this product?



DC Axial Fans - 15050VA-24N-EL-00



Get a sample

Resources

Specification Sheet	Series Data Sheet
Certificates	RoHS Certificate



Specifications

Category	DC Axial Fans
Part Number	15050VA-24N-EL-00
Frame Width [mm]	150
Frame Height [mm]	172
Frame Depth [mm]	50

Max. Air Flow [CFM]	261.32
Max. Air Flow [m3 per min]	7.4
Max. Static Pressure [In H2O]	0.735
Max. Static Pressure [Pa]	183
Fan Speed [RPM]	3500
Noise [dB]	60
Life Expectancy [L10]	100,000 hours at 25C
Bearing Type	Ball Bearing
Nominal Voltage [V]	24
Operating Voltage - Lower [V]	18
Operating Voltage - Upper [V]	26.4
Current [A]	0.9

Input Power [W]	21.6
Mass [g]	750
Tach / Locked Rotor Output	Locked Rotor
Status	Active

PRODUCTS[See All Products](#) →[Find A Distributor](#)[Find a Sales Representative](#)**INDUSTRIES**[See All Industries](#)[Automotive](#)[Industrial](#)[Medical](#)[Consumer Technology](#)[Smart City](#)[Lighting Innovations](#)**RESOURCES**[See All Resources](#) →[Application Notes & Whitepapers](#)[Latest News](#)[Videos](#)**CONTACT****NMB Technologies Corporation****(248) 919-2250****info@nmbtc.com**

Have A Question?

Our precision component experts can help you find the right solutions.

[Contact Us Today](#)[Find A Distributor](#)[Find Sales Rep For Fans](#) →

