

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [11938MA-48P-EA-D0](#)[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 11938MA-48P-EA-D0


[Get a sample](#)

Resources

[Specification Sheet](#)[Series
Data
Sheet](#)



←











→

Specifications

Category	DC Axial Fans
Part Number	11938MA-48P-EA-D0
Frame Width [mm]	119
Frame Height [mm]	119
Frame Depth [mm]	38.4

Max. Air Flow [CFM]	181
Max. Air Flow [m3 per min]	5.13
Max. Static Pressure [In H2O]	0.85
Max. Static Pressure [Pa]	213
Fan Speed [RPM]	4700
Noise [dB]	59.5
Life Expectancy [L10]	25 degree C 100,000 Hours (D00)
Bearing Type	Ball Bearing
Nominal Voltage [V]	48
Operating Voltage - Lower [V]	30
Operating Voltage - Upper [V]	52.8
Current [A]	0.49

Input Power [W]	23.5
Mass [g]	400
Tach / Locked Rotor Output	No
Status	Active

PRODUCTS[See All Products](#) →[Find A Distributor](#)[Find a Sales Representative](#)**INDUSTRIES**[See All Industries](#)[Automotive](#)[Industrial](#)[Medical](#)[Consumer Technology](#)[Smart City](#)[Lighting Innovations](#)**RESOURCES**[See All Resources](#) →[Application Notes & Whitepapers](#)[Latest News](#)[Videos](#)**CONTACT**

NMB Technologies Corporation

(248) 919-2250

info@nmbtc.com

Have A Question?

Our precision component experts can help you find the right solutions.

[Contact Us Today](#)[Find A Distributor](#)[Find Sales Rep For Fans](#) →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)[Careers](#)[Sitemap](#)[Privacy Policy](#)[Terms of use](#)

