

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [04010SA-12M-AT-D0](#)[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 04010SA-12M-AT-D0

[Get a sample](#)

Specifications

Category	DC Axial Fans
Part Number	04010SA-12M-AT-D0
Frame Width [mm]	40

Frame Height [mm]	40
Frame Depth [mm]	10
Max. Air Flow [CFM]	5.6
Max. Air Flow [m3 per min]	0.16
Max. Static Pressure [In H2O]	0.15
Max. Static Pressure [Pa]	37
Fan Speed [RPM]	6500
Noise [dB]	24.5
Life Expectancy [L10]	50,000 hours at 40C
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	10.2
Operating Voltage - Upper [V]	13.8

Current [A]	0.05
Input Power [W]	0.6
Mass [g]	16
Tach / Locked Rotor Output	Tach Output
Status	Active

PRODUCTS

[See All Products](#) →
[Find A Distributor](#)
[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#)
[Automotive](#)
[Industrial](#)
[Medical](#)
[Consumer Technology](#)
[Smart City](#)
[Lighting Innovations](#)

RESOURCES

→ [See All Resources](#) →
[Application Notes & Whitepapers](#)
[Latest News](#)
[Videos](#)

CONTACT

NMB Technologies Corporation
[\(248\) 919-2250](#)
info@nmbtc.com

Have A Question?

Our precision component experts can help you find the right solutions.

Contact Us Today

Find A Distributor

Find Sales Rep For Fans →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)

[Careers](#)

[Sitemap](#)

[Privacy
Policy](#)

[Terms of
use](#)