productinformation

tesa® 51006

PET cloth tape for abrasion protection

tesa® 51006 is a PET cloth wire harness tape with a rubber based adhesive.

Major Features:

- High temperature resistance 150°C/3000h
- Abrasion resistant
- Strong adhesion

Color: Available in black

Main Application

tesa® 51006 is designed for the engine compartment, providing abrasion protection.

Technical Data

Backing material	PET cloth		Temperature resistance (3000h)	150 °C
Total thickness	320 μm		Abrasion resistance (10mm	Class C (acc. to
Type of adhesive	rubber based		mandrel)	LV312)
Adhesion to steel	4.5 N/cm		Abrasion resistance (5mm	Class B (acc. to
Elongation at break	22 %		mandrel)	LV312)
Tensile strength	175 N/cm		Flame resistance as composite	Class B (acc. to
Temperature resistance min.	-40 °C			LV312)
			Unwind force (roll width ≤ 9mm)	6 N/roll (30 m/min)
			Unwind force (roll width > 9mm)	10 N/roll (30 m/min
		•	Noise damping (decibel)	Class A (acc. to

n) LV312)

Additional Information

- Technical data acc. to LV 312
- Applicable for red ring assembly aid