

tesa® 51914



Product Information

Repulpable double-sided splicing tape

tesa® 51914 is a double-sided repulpable tape consisting of a tissue paper backing and a modified water soluble acrylic adhesive.

tesa® 51914 features especially

- Highest tack properties
- Very good adhesion values on coated and uncoated papers
- Good shear strength
- Good repulpability over full pH-range (pH3 –pH9)

Colour: Blue, Colourless

Main Application

tesa® 51914 is particularly suitable for

- Flying splices in the printing and paper producing industry

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	non-woven	• Type of liner	repulpable
• Total thickness	90 µm	• Shelf life time (packed) < 25°C	siliconised paper
• Type of adhesive	repulpable tackified acrylic		12 months

Properties

- | | | | |
|--------|------|---------------------------|------|
| • Tack | ●●●● | • Static shear resistance | ●●●● |
|--------|------|---------------------------|------|

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

tesa® 51914

Product Information



Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=51914>