

tesa® 60955



Anti-Slip Tape Conformable

Product Information

Conformable Anti-Slip Tape for Irregular Surfaces

tesa® 60955 is an anti-slip tape with a conformable backing and designed for adhering to tread plates and other irregular surfaces where good grip and safe footing is required. The conformable anti-slip tape is a single-sided tape, with a PET-liner, in form of a conformable, hand-tearable anti-slip backing with an acrylic adhesive. The backing consists of an aluminum carrier which is coated with mineral particles and has been specifically developed to conform around edges and adhere to irregular surfaces. The acrylic adhesive provides an excellent bond to most surfaces.

tesa® 60955 is certified according to DIN 51130 and available in the colors black, yellow and black-yellow. The bright yellow and black-yellow colored tapes have a strong visibility for easy identification in areas of safety concerns and for warning purposes, a perfect solution for complementing 5S manufacturing initiatives.

Benefits:

- Backing with good slip resistance and excellent conformability
- Perfectly conforms around edges, corners and adheres to irregular surfaces
- Slip resistance R13 according to DIN 51130
- Good chemical and weathering resistance
- Secure bonding to most surfaces
- Bright yellow and black-yellow colors ensure strong visibility for easy identification

Main Application

- tesa® 60955 is recommended for irregular surfaces where good grip and safe footing is required, e.g. tread plates, fire escape ladders, loading ramps and platforms
- The conformable anti-slip tape can be used to cover flat surfaces with e.g. screw heads or rivets
- tesa® 60955 is a perfect solution for complementing 5S manufacturing initiatives

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	Aluminum carrier coated with mineral particles	• Elongation at break	12 %
• Total thickness	750 µm	• Tensile strength	60 N/cm
• Thickness of tape	700 µm	• Thickness of liner	50 µm
• Type of adhesive	acrylic	• Temperature resistance	-5 to +120 °C

Adhesion to

- steel 8.0 N/cm

tesa® 60955



Anti-Slip Tape Conformable

Product Information

Properties

- Hand tearability ●●●
- Suitable for die cutting yes
- Resistance to chemicals ●●●
- Salt water resistant ●●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=60955>