

# tesa® double-sided tape

## Features

- Double-sided adhesive tape with transparent PP base
- Solvent-free adhesive
- High adhesive power
- Long-lasting
- Usable without hand dispenser
- Length of roll: 10 m, width of adhesive tape: 12 mm

## Product Properties

• Applicationfield	Home	• Recyclable	no
• Tear resistant	yes	• Shape	Roll
• Humidity resistant	no	• Batteries required	no
• Solvent free	yes	• Batteries included	no
• Suitable surfaces	Tiles, Glass, Plaster, Steel, Stone, Brick, Acrylic glass, Metal, Most plastics, Paper, Cardboard		

## Technical Data

• Ecofriendly packaging	no	• Total thickness	175 µm
• Residue-free removable	no	• Temperature resistant	yes
• Adhesive strength	High adhesion	• Tensibility	25 %
• Type of adhesive	synthetic rubber		

## Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=64621>