

## Product Information

### Tensilised Strapping Tape

tesa® 4224 is a tensilised poly-propylene strapping tape with a natural rubber adhesion system and was specially developed for the food and drug industries. tesa® 4224 exhibits good ten-sile strength and low elongation at the same time. The product has a clean appearance, is highly cold-resistant and, therefore, ideal also for frozen food packaging.

### Main Application

Applications include closure of shipping cartons, palletising, bundling, reinforcing and unitising.

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

• Backing material	MOPP	• Elongation at break	35 %
• Total thickness	79 µm	• Tensile strength	180 N/cm
• Type of adhesive	natural rubber		

#### Adhesion to

• steel	4.0 N/cm
---------	----------

#### Properties

• Residue free removal	Yes	• No discolouration	Yes
------------------------	-----	---------------------	-----

### Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

