

# tesa® 4316 PV3



## Product Information

Finely crêped paper masking tape for paint spraying

tesa® 4316 is a finely crêped paper masking tape. The product is thin and flexible and suitable for all general masking applications as well as oven drying applications up to a temperature of 100 °C.

### Main Application

The product is resistant to wet sanding. Paints and fillers adhere well to the backing.

The material can be used on painted metal, rubber, glass and chrome parts.

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

• Backing material	slightly-creped paper	• Elongation at break	10 %
• Total thickness	140 µm	• Tensile strength	38 N/cm
• Type of adhesive	natural rubber	• Temperature resistance	100 °C

#### Adhesion to

• steel	3.4 N/cm
---------	----------

#### Properties

• Hand tearability	●●●●	• Sharp colour edge	●●●
• Easy to remove	Yes	• Conformability	●●●
• Paint anchorage	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

# tesa® 4316 PV3

## Product Information



### Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=04316>