

Product Information

Strongly crêped paper masking tape for painting and packaging

tesa® 4319 is a highly crêped, general purpose paper masking tape for various application fields.

Main Application

It is particularly suited for masking during paintwork, for underbody sealing and bundling as well as for edge protection of paper reels. The product offers a good tack.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	highly-creped paper	• Elongation at break	58 %
• Total thickness	375 µm	• Tensile strength	24 N/cm
• Type of adhesive	natural rubber		

Adhesion to

• steel	4.5 N/cm
---------	----------

Properties

• Hand tearability	●●●●	• Paint anchorage	●●●●
• Suitable for rough surfaces	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

Additional Information

Recommendation:

Stretching the crêped backing guarantees evenly defined paint edges and a good adhesion.

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=04319>