

tesa® Professional 4368



Product Information

2-in-1: Masking film with surface protection tape

With the masking film of tesa Easy Cover® Universal (incl. tesa® 4316 premium masking tape) you will save both time and effort. Because with the practical 2-in-1 solution you can protect your surroundings quickly and safely in only one working step. Cover up even large surfaces in no time – furniture, floors or walls – thanks to the straightforward handling of the different formats. With tesa Easy Cover® Universal, you are well equipped to pave the way for outstanding painting work. In combination with your skilled craftsmanship, you will achieve results that will impress your customers.

Main Application

- Indoor masking
- The 2-in-1 solution for masking off and protecting large areas
- Clean edges to paint and lacquer
- For smooth and slightly textured surfaces
- For painting tasks and spray techniques

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

- | | | | |
|---------------------------------|-----------------------|--------------------------------|---------|
| • Backing material | slightly-creped paper | • Elongation at break | 10 % |
| • Color | pale cream | • Tensile strength | 38 N/cm |
| • Total thickness | 140 µm | • UV-resistance | 1 weeks |
| • Thickness of masking coverage | 10 µm | • Material of masking coverage | HDPE |
| • Type of adhesive | natural rubber | | |

Adhesion to

- steel 3.4 N/cm

Properties

- | | | | |
|-----------------------------------|------|--------------------|-----|
| • Suitable for sensitive surfaces | ●● | • Sharp color edge | ●●● |
| • Suitable for rough surfaces | ●●● | • Conformability | ●● |
| • Paint anchorage | ●●●● | | |

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

tesa® Professional 4368

Product Information



Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=04368>