

Product Information

Cloth duct tape - 8 weeks UV resistance

tesa® 4370 is a cloth duct tape for professionals. It can be easily torn by hand both crossways and lengthways and offers impressive adhesive strength. It consists of a fabric substrate and a natural rubber adhesive mass. Thanks to its high degree of UV resistance, the waterproof cloth duct tape can be used outdoors for up to 8 weeks at a time. tesa® 4370 is very easy to handle and is your reliable partner for house building and other construction projects.

Benefits:

- High UV resistance (up to 8 weeks) and water-repellent
- Good adhesion even to rough surfaces
- Residue-free removability for masking applications
- Conformable and easy to unwind

Main Application

- tesa® 4370 is recommended for the protection of areas like window frames or facades during construction works
- The cloth tape is used for the protection against dirt and damage through manufacturing tools and material
- tesa® 4370 is suitable for application on concrete/ bricks, timber, glass or other outdoor applications (up to 8 weeks)

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	cloth	• Tensile strength	60 N/cm
• Total thickness	310 µm	• UV-resistance	8 weeks
• Type of adhesive	natural rubber	• Mesh	70 count per square inch
• Elongation at break	10 %		

Adhesion to

- steel 3.8 N/cm

Properties

• Hand tearability	●●●●	• Paint anchorage	●●●●
• Suitable for sensitive surfaces	●●●●	• Conformability	●●●●
• Suitable for rough surfaces	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

Additional Information

We recommend to conduct a test on the application surface before using the product.

tesa® 4370

Product Information



Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=04370>