



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on




requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-T319-T273
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB



TE Part # 2005330-1
025/090/110 HYB 24P CAP ASSY



TE Part # 1376109-3
025 TAB CONT AS



TE Part # 2005154-2
025 TAB CONTACT(S) GOLD



TE Part # 1376607-2
025 TAB CONT L/P GOLD

Also in the Series | TH/.025 Connector System



Automotive Connector Caps & Covers
(6)




Automotive Housings(206)



Automotive Seals & Cavity Plugs(2)




Automotive Terminals(31)



Insertion & Extraction Tools(4)



Other Automotive Connector
Accessories(5)




PCB Connector Headers & Receptacles
(147)

Customers Also Bought





TE Part #1891600-1
EXTRACTION TOOL



TE Part #1276565-1
EXTRACTION TOOL FOR .025 REC



TE Part #1-1579007-2
EXTRACTION TOOL



TE Part #9-1579028-2
EXTRACTION TOOL

TE Part #2-1999775-0
0.5/1.5HYBRID CONN. ASSY M/C 28P

TE Part #2-1999775-5
0.5/1.5HYBRID CONN. ASSY M/C 38P

TE Part #2088128-5
HEIGHT GAUGE,HYBRID CONN

TE Part #2088128-6
HEIGHT GAUGE,HYBRID CONN

TE Part #2155562-1
STUFFER WIRE

TE Part #4-539229-1
SHEAR BLADE

Documents

Product Drawings
EXT-TOOL FOR 025 TAB

English

Datasheets & Catalog Pages
Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Insertion-Extraction-Tool-2345721-1

English

Instruction Sheets
The extraction tool for AMP 025 tab contact

English

Instruction Sheet (non U.S.)

English