



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**  
Ratchet Configuration: **Operator Releasable & Adjustable**  
Die Sets Type: **Removable/Interchangeable**  
Specification Type: **TE Product Specification (114-)**  
TE Certification: **Upon Request for Fee**

Features

Other

|                             |                                  |
|-----------------------------|----------------------------------|
| Crimp Form-Wire Barrel Type | Open Barrel - F Crimp            |
| Tool Grade                  | Commercial Crimp Tooling         |
| Ratchet Configuration       | Operator Releasable & Adjustable |
| Die Sets Type               | Removable/Interchangeable        |
| Specification Type          | TE Product Specification (114-)  |
| TE Certification            | Upon Request for Fee             |
| Power Technology Type       | Battery, Electric, Manual        |
| Tooling Type                | PRO-CRIMPER Hand Tool            |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Out of Scope  |
| EU ELV Directive 2000/53/EC                   | Out of Scope  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUL 2021 (219)<br>Candidate List Declared Against: JAN 2021 (211)<br>SVHC > Threshold:<br>Not Yet Reviewed |









|                           |  |
|---------------------------|--|
| Halogen Content           | Not Yet Reviewed for halogen content         |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|   |  |   |   |
|---|--|---|---|
|  <p>TE Part # CAT-AM705-T273<br/>AMP MCP, RECEPTACLE AND TAB</p> |  <p>TE Part # CAT-AM706-T273<br/>AMP MCP, SFC, RECEPTACLE</p>  |  <p>TE Part # 1-968876-1<br/>AMP MCP 2.8, CONTACT SWS (LP)</p> |  <p>TE Part # 1-968875-3<br/>AMP MCP 2.8, CONTACT SWS (LP)</p> |
|  <p>TE Part # 1-968876-3<br/>AMP MCP 2.8, CONTACT SWS (LP)</p>   |  <p>TE Part # 1-968875-2<br/>AMP MCP 2.8, CONTACT SWS (LP)</p> |   |   |

Customers Also Bought

|  |  |  |   |
|--|--|--|---|
|  <p>TE Part #964971-1<br/>EINZELLEITERDICHUNG</p> |  <p>TE Part #1-968855-1<br/>AMP MCP 2.8, CONTACT SWS</p> |  <p>TE Part #1670144-1<br/>MCON 1.2 CB REC SRC SN</p> |  <p>TE Part #539635-1<br/>ERGO HAND TOOL FRAME-NO DIES</p> |
|--|--|--|---|





TE Part #1-1579007-1  
EXTRACTION TOOL



TE Part #C02462-000  
VERSAFIT-1/2-KT1-REFILL



TE Part #2305570-1  
TERMINAL CUTTER, SIDE FEED



KIT  
TE Part #7-2150805-7  
OC-100F180F-CRIMPTOOLINGKIT



KIT  
TE Part #7-2151515-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-026F027F



TE Part #785863-1  
TOOL FOR 24W MCP MALE CONN. SEC. LOCK

Documents

Datasheets & Catalog Pages

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

Commercial Portable Crimp Tooling 1-1773865-2

English

Instruction Sheets

Instruction Sheet (U.S.)

English