

CREALITY

CR-6 MAX Basic Repair Kit

Complete maintenance equipment



CR-6 Max Basic Repair Kit

MFR: 4006010019

Product Information

CR-6 MAX Basic Repair Kit
Complete Maintenance Equipment

CR-6 MAX Basic Repair Kit

Complete maintenance equipment



CR-6 MAX Repair Kit



Screws list

Hexagon socket head screw

...



(M5*40)*1 (M5*30)*2 (M5*30)*1 (M5*20)*1



(M3*25)*1 (M4*18)*1 (M4*20)*1 (M3*16)*1



(M5*12)*1 (M5*10)*2 (M4*12)*1 (M3*10)*1



(M4*6)*1 (M3*8)*4 (M3*6)*2 (M3*4)*1

Hexagon socket cylindrical head screw

• • •



(M3*25)*1

(M4*20)*1

(M4*18)*1

(M3*18)*1

(M3*16)*1



(M3*14)*1

(M3*10)*1

(M2*12)*1

(M2*10)*1



Hexagon socket countersunk head screws



(M3*40)*1



(M4*25)*1



(M4*20)*3



(M3*20)*1



(M3*12)*1



(M3*8)*1



Hexagon socket cylindrical head
combination screw with spring washer

• • •



(M5*45)*1

(M5*18)*1



Others



Union bolt (M6*35)*1

Full thread stud (M6*40) *2



Locknut M3*2



Locknut M5*2



Hexagon nut M6*2



T-ship type screw M5*2



Cross recessed pan head
tapping screws(ST3*8)*1



Hexagon socket set screw
with flat end(M3*3)*2



Cables and wires



14+16P Flat cable
L=1520/900mm



motor line+limit line
L=720/850mm



Z2 axis motor line L=800mm



Z1 axis motor line L=430mm



Display line L=650mm



Power red and black
wires L=720mm



X axis limit line L=150mm



Optoelectronic switch wire L=300mm



Red silicone wire L=110mm



Red silicone wire (short connection) L=90mm



Ground wire L=120mm



Black silicone wire L=110mm



X axis motor line L=100mm



E axis motor line L=60mm



Breakage detection wire L=100mm



Optocoupler switch strip wire L=40mm



Wire to board connector
(1*4P) *2 (1*3P) *1 (1*3P) *1 (1*2P) *1



Textured paper



Black nylon cable tie

Item Name	Spec.	Quantity	Unit
Hexagon socket countersunk head screw	M3*20, SUS304, ROHS	1.00	PCS
Hexagon socket countersunk head screw	M3*12, 40CR, black, ROHS	1.00	PCS
Hexagon socket countersunk head screw	M3*40, 40CR, black, ROHS	1.00	PCS
Hexagon socket countersunk head screw	M4*20, SUS304, ROHS	3.00	PCS
Hexagon socket countersunk head screw	M3*8, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M4*18, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M3*8, SUS304, ROHS	4.00	PCS
Hexagon socket flat round head screw	M5*40, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M5*30, SUS304, ROHS	2.00	PCS
Hexagon socket flat round head screw	M5*20, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M5*12, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M5*10, SUS304, ROHS	2.00	PCS
Hexagon socket flat round head screw	M4*20, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M4*12, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M3*25, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M3*16, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M3*10, SUS304, ROHS	1.00	PCS
Hexagon socket flat round head screw	M3*6, SUS304, ROHS	2.00	PCS
Hexagon socket flat round head screw	M3*4, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M4*18, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*10, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M4*20, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*25, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*18, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M3*16, 40CR, black, ROHS	1.00	PCS
Hexagon socket head screw	M2*10, 40CR, black, ROHS	1.00	PCS
T shape ship nut	M5, ROHS	2.00	PCS
Locking nut (nylon inserted)	M5, SUS304, ROHS	2.00	PCS
Locking nut (nylon inserted)	M3, SUS304, ROHS	2.00	PCS
hex nut	M6, SUS304, ROHS	1.00	PCS
Cross recessed pan head tapping screw	ST3*8, SUS304, ROHS	1.00	PCS
Hexagon socket head spring pad set screw	M5*45, 40CR, black, ROHS	1.00	PCS
all threaded stud	M6*40, SUS304, ROHS	2.00	PCS
swing bolt	M6*35, d5.2, SUS304, ROHS	1.00	PCS
Hexagon socket set screw with flat end	M3*3, 40CR, black, ROHS	2.00	PCS
textured paper	W-100mm	1.00	Roll
Wire-to-board connector	Wire-to-board connector, XH2.54-3P, 1*3P, white	1.00	PCS
Red silicone wire (short connection)	L90mm	1.00	PCS
Hexagon socket flat round head screw	M4*6, 40CR, black, ROHS	1.00	PCS
Hexagon socket flat round head screw	M5*30, 40CR, black, ROHS	1.00	PCS
E motor line	1007/24AWG, 11/0.14±0.008TS4P coupling, black, L60mm	1.00	PCS
Hexagon socket head screw	M3*14, SUS304, ROHS	1.00	PCS
Hexagon socket head screw	M2*12, SUS304, ROHS	1.00	PCS
Hexagon socket countersunk head screw	M4*25, SUS304, ROHS	1.00	PCS
Motor line	X axis motor cable, 4P black coupling, 24AWG, L100mm	1.00	PCS
Motor limit line	X axis limit cable, 2P black coupling, 24AWG, L150mm	1.00	PCS
Extension cord	filamet detation extension cord, 3P black, 24AWG, L100mm	1.00	PCS
Power supply cable	power supply cable, 3P black, 24AWG, L300mm	1.00	PCS
Hexagon socket head spring pad set screw	M5*18, 40CR, black, ROHS	1.00	PCS
optocoupler switch with wire	L40mm	1.00	PCS
optoelectronic switch	optoelectronic switch	1.00	PCS
black Nylon cable ties	4*150mm, black, 100pcs	1.00	PCS
Display line	1007/24AWG, 6P, black, L650, 2.54-6P terminal and 2.54-6P terminal	1.00	PCS
Power supply red black cable	3135/14AWG, L720mm	1.00	PCS
14+16P flat cable	26AWG, black PVC cable, 16Pin(L1520)+14Pin(L900)	1.00	PCS
motor cable+ limit cable	6P black, L720	1.00	PCS
Z1 axis motor cable	1007/24AWG, 4P black, L430mm	1.00	PCS
Z2 axis motor cable	1007/24AWG, 4P black, L800mm	1.00	PCS
black silicone wire	3135/14AWG, black, L110	1.00	PCS
Red silicone wire	3135/14AWG, red, L110	1.00	PCS
ground electrode	1007/16AWG, yellow green cable, L120	1.00	PCS