pro-signal

RoHS

Compliant



Specifications


Connector Type A Connector Type B Jacket Colour

: DisplayPort Plug

: DVI-I Plug

: Black

Diagram



No.	Material	Description	Qty	Unit
1	Cable	(7/0.127TC×1P+7/0.127TC=FAM)×5+(7/0.127TC)×5C+AL-Foil+Drain Wire+(1/0.32BC)+Braid(80/0.12AL-MG) Black PVC Jacket, OD: 7.3±0.2mm	- mm	
2	Connector	DVI (24+1) Male the pin gold plated, White insulation, Gold plated shell PCBA+(IC:PS8121E)	1	Pcs
3	Connector	DP Male the Pin Gold Plated, Black Insulation, Gold Plated Shell		
4	Thumb Screw	#40-40 B-L38 Black PVC	2	
5	Molded	LD-PE		g
6	Molded	45P Black PVC] -	
7	Plastic Hood	DP Male Black ABS	1	Set

Part Number Table

Description	L ±T (mm)	Part Number
	500 ±15	PSG04045
	1000 ±20	PSG04046
DisplayPort Plug to DVI-I Plug, Black	2000 ±40	PSG04047
	3000 ±60	PSG04048
	5000 ±100	PSG04049

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for white any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

