

AMP | AMP CPC

TE Internal #: 206060-2

AMP CPC, Circular Power Connectors, Housing, Operating Voltage 600 VDC, Wire-to-Wire, 4 Position, Wire & Cable, Plug, Socket,

Signal, Black

View on TE.com >



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Connector Product Type: Housing

Operating Voltage: 600 VDC

Connector System: Wire-to-Wire

Number of Positions: 4

Sealable: No

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	4
Number of Power Positions	0
Keying	A
Number of Signal Positions	4

Electrical Characteristics

Contact Features

Reverse Gender	No
Contact Type	Socket
Contact Current Rating (Max)	13 A



Contact Protection With

Mechanical Attachment

Panel Mount Feature Type Flange

Screw & Hole Thread Size 5/8-24 UNEF-2A

Mating Alignment With

Mating Retention With

Panel Mount Feature Without

Mating Alignment Type Keyed

Mating Retention Type Threaded Coupling

Housing Features

Body OrientationStraightHousing ColorBlackHousing MaterialPA 6.6 GF

Circular Connector Shell Size 11

Usage Conditions

Operating Temperature Range -55 – 105 °C[-67 – 221 °F]

Fluid Resistance None

Operation/Application

Circuit Application Signal

Shielded

Industry Standards

UL Flammability Rating

UL 94V-0

VDE Tested No

Packaging Features

Packaging Method Small Pack

Packaging Quantity 100

Other

Comment Small Pack

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU Compliant



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)





Circular Connector Keying Plugs(2)



Circular Connector Seals(36)



Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #206061-1 RECPT, SZ 11-4, CPC



TE Part #1-66359-4

TYPE III CONTACTS STRIP



TE Part #1-206062-4

CABLE CLAMP KIT #11



TE Part #320383 TERMINAL,SOLIS R 2 1/4



TE Part #211149-1
PIN HSG,25 POSN,METRIMATE



TE Part #770071-1 03P .093 COMM P&S RECPT HSG



TE Part #4-1393117-3 KUP-11D15-110=KU



TE Part #2217347-1 LED WORKLIGHT ASSY

Documents



Product Drawings

CPC PLUG,SZ 11-4,SMALL PACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_206060-2_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_206060-2_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_206060-2_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

Product Specifications

Connector, Circular Plastic

English

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

CSA Certificate

English