




Connectors > Circular Connectors > Circular Connector Accessories > Unscreened Circular Connector Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Clamp**
Compatible With Circular Connector Shell Size: **17**
Body Orientation: **Straight**
Accepts Cable Diameter (Max): **11.51 mm [.453 in]**
Protective Cover: **Without**

Features

Product Type Features

Product Type	Accessory
Backshell & Clamp Accessory Type	Cable Clamp
Protective Cover	Without

Body Features

Cable Clamp Material	Nylon
Cable Clamp Flammability Rating	UL 94V-1
Cable Clamp Color	Black

Mechanical Attachment

Screw & Hole Thread Size	15/16-20
--------------------------	----------

Housing Features

Body Orientation	Straight
------------------	----------

Dimensions

Accepts Cable Diameter (Max)	11.51 mm[.453 in]
------------------------------	-------------------

Operation/Application

Compatible With Circular Connector Shell Size	17
---	----

Packaging Features

Packaging Quantity	100
Packaging Method	Bulk



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 213906-1
CPC PLUG ASSY, SRS 6, SZ 17-10



TE Part # 213905-1
CPC PLUG ASSY, SERIES 5, SZ 17-3



TE Part # 213899-1
CPC SEAL ASSY KIT, SRS 5, 17-3

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)




Circular Connector Seals(36)



Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)


Customers Also Bought



TE Part #206044-1
CPC PLUG ASSEMBLY SIZE 17-14



TE Part #2-36153-5
TERMINAL,PIDG R IR 18 10




TE Part #213671-1
CPC 18-10 PLUG KIT W/CPLG RING



TE Part #2119142-1
CCII D1000 2L REC TAB 22-18 ASSY



TE Part #213905-1
CPC SERIES 5



TE Part #213847-1
POWERBAND CONT ASSY,SILVER PLT



TE Part #882218-000
SO63-5-55-22-90



TE Part #202236-1
III+ PIN,SOLTAB,30AU,10AU FLASH,LP



Documents

Product Drawings

CPC CBL CLMP KIT,STD,SZ17,BULK

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_213904-4_A.3d_stp.zip

English

Customer View Model

ENG_CVM_213904-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_213904-4_A.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English