
1.27mm IDC Conenctor DIP Type

multicomp PRO

RoHS

Compliant





opeenieuleile	
Current Rating	: 1.2A AC
Voltage Rating	: 250V A
Contact Resistance	: 20m Ω
Insulation Resistance	: 1,000M
Withstanding Voltage	: 500V A
Operating Temperature	: -40°C to


Materinal


Insulator Colour Terminal Plating

- C/DC
- C/DC Max.
- IΩ Min.
- C/minute
- o +105°C


: High Temp. Plastic (Nylon46 UL94V-0

- : Black
- : Copper Alloy
- : Tin Plated






1.30



Part Number Table



Dimensions : Millimetres

Description	Positions	A (mm)	B (mm)	Part Number
IDC Conenctor, Vertical, 1.27mm, DIP	6	11.4	6.35	MP008695
	8	13.94	8.89	MP008696
	10	16.48	11.43	MP008697
	12	19.02	13.97	MP008698
	14	21.56	16.51	MP008699

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

