Acoustic Signals - Industrial **PIEZO BUZZERS**



Acoustic Signals Piezo Buzzers > **AE20M Series**

Product overview


The AE20M piezo miniature buzzer range is a compact, low cost audible signalling solution for local indication where very low current consumption may be a requirement. A threaded

locking ring allows for easy installation for all panel mount installations.

The unit offers a single stage alarm, either a fast pulsed or continuous tone selectable by a three pin connection combination.


AE20M Series > Ordering Information

Code No:	Voltage:	Frequency:	Current:	dB:
AE20M-12	10-20v Dc	2900 Hz	25 mA	90
AE20M-24	10-28v Dc	2900 Hz	25 mA	85
AE20M-48	6-48v Dc	2900 Hz	35 mA	82
AE20M-115	60-120v Ac ~	2900 Hz	25 mA	90
AE20M-230	130-240v Ac ~	2900 Hz	25 mA	90
Frequency +/- 5	500 dB at prime v	oltage +/- 3dB		
Kg 0.08 ∕_50/60		0 Hz	C -20+60	IP 55
APPROVALS CONFORMIT		BOHS	(€	



Connections for 115v & 230v Tone Terminals Pulsed A + B Continuous A+C

Connections for 12v to 48v Tone Terminals Pulsed B + A Continuous B + C



- · Continuously rated
- Economical
- Suitable for panel mounting only
- Two tone sound option
- Wide operating voltage •
- Compact design
- · Locking ring allows for easy installation

ABS Plastic

dB 80/90

