Visual Signals - Industrial

LIGHT EMITTING DIODE BEACONS



Industrial LED Flashing Rotating Static Beacons > LED201/200 Series

Product overview

The LED201/200 series are suitable for security, process control & industrial applications, where low maintenance and long life are the pre-requisite requirement.

These beacons offer four modes of operation selected by a four way switch on the PCB:

- 1. Continuous mode
- 2. Flashing mode at 1Hz
- 3. Rotating mode: Twin column
- 4. Rotating mode: Single column

An advantage of the continuous mode is that it can be controlled via a remote source (ie. control panel / plc etc) offering the potential of a remote flashing option. The design allows for termination inside the enclosure through the base.

156mm 205mm 49mm 115mm 2 x 5mm x 3 holes x 96 PCD to accept No 6

self tap screw (external fitting)

- Continuously rated
- Incorporates an 144 off extra bright LED array
- Suitable for surface, conduit box or wall mounting
- · Optional wall bracket & guard available - see accessories
- 360° light output around the vertical axis.
- Dustproof and Weatherproof

LED201/200 Series > Ordering Information

Code No:	Voltage:	Colours:	Current:		
LED201-02	24v Dc	Red & Amber Green, Blue & Clear	Flashing 210mA 115mA	Rotating 130mA 50mA	Static 440mA 230mA
LED200-04 •	90-370v Dc 70-265v Ac ~	Red & Amber Green, Blue & Clear	110/55mA 65/40mA		200/100mA 120/59mA

All Colours @ 115/230v Ac ~

Red/Amber in Static Mode @ 280v Dc is 40mA

ADD THE FOLLOWING LENS CODES TO THE PRODUCT WHEN ORDERING





Note: Current consumption is an average over a 60 second cycle









UV Stable Polycarbonate Lens

UV Stable ABS Plastic Base

Kg $^{0.52}_{0.47}$ **Ac** $^{0.52}_{Dc}$











RPM 140













